TELEDYNE FLIR

# LVSS ADA C-UAS

Mobile Surveillance with Air Domain Awareness (ADA) and Counter-UAS (C-UAS) Capabilities

## APPLICATIONS

- FORCE PROTECTION
- BORDER SURVEILLANCE
- TACTICAL RECONNAISSANCE
- PIPELINE SECURITY
- MOBILE COMMAND CENTER
- MOBILE SECURITY
- TARGET TRACKING
- LONG RANGE SURVEILLANCE



LVSS C-UAS adds proven Air Domain Awareness and Counter-UAS capabilities to the market-leading LVSS platform. LVSS C-UAS utilizes 3D Radar, EO/IR Camera, and RF detection and mitigation sensors to provide early warning alerts, detection, and non-kinetic countermeasures for various UAS systems. Threats are detected and displayed simultaneously, with position and elevation available for all radar tracks. The system is standalone, relocatable, and rapidly deployable.

Cameleon software provides advanced command and control (C2) capabilities, allowing individual control of sensors along with automated point-and-click or slew-to-cue functionality. Fixed sector, alternating sector, or continuous scan are the various radar operation sets. LVSS C2 leverages man-in-loop autonomy and artificial intelligence/machine learning (AI/ML) to identify targets, classify threats, cue RF sensors, and streamline the decision cycle.

All sensors and effectors are high technology readiness level (TRL) as currently implemented. The base LVSS system can be retrofit in the field to add ADA or C-UAS configurations to meet user requirements.

## FEATURES

### RAPID RELOCATION PERIMETER PROTECTION

The LVSS system is rapidly deployable (and stowed) to provide relocatable surveillance solutions to large areas. The sensors integrate to allow complete hemispherical detection of land and air targets.

### ON-THE-MOVE EFFECTIVE, NON-KINETIC COUNTERMEASURES

Non-kinetic RF countermeasures provide the system with full C-UAS kill chain capabilities. Threats are detected simultaneously. Details are provided to the operator when the system is either fully deployed or while the vehicle is on-the-move.

### ACT FASTER WITH HIGH PERFORMING VIDEO ANALYTICS

Gain additional insight into selected threats by engaging comprehensive video analytics models to identify and track. The analytics model can be used to control the camera autonomously.

### INTEGRATE COMPLEX SYSTEMS, OPTIMIZING AWARENESS ACROSS DOMAINS

Cameleon integrates with operational features from all onboard sensors. It supports advanced device features and bi-directional communications.

### REDUCE CYBER RISK

A cyber security tool provides high resistance to hacker attacks that can compromise mission effectiveness.

TELEDYNE FLIR

## SPECIFICATIONS

| ARCHITECTURE | |
|---|---|
| Base Platform | Ford F-250 Standard Truck |
| **Size** | |
| Weight | Approx. 7,700 lbs. (3,500 kg) |
| Length | Approx. 265 in. (673 cm) |
| Width | Approx. 100 in. (254 cm) |
| Height (mast stowed) | 22 in. (56 cm) |
| Height (mast deployed) | 16 ft. (4.9m) from ground to center of camera for Ford F-250 |
| **Radar and EO/IR Sensors** | |
| Radar Standard Option | R20SS-3D Long Range Ground Surveillance Radar |
| Camera Standard Option | TacFLIR-380HD |
| Camera Wavelength Options | High Definition (HD) Mid-Wave Infrared (MWIR), Short Wave Infrared |
| Lasers | Laser Rangefinder<br>Laser Pointer (NIR wavelength) |
| Illuminators | NIR wavelength |
| Other Sensors | Differential GPS, Weather Station, Inclinometers, Perimeter Intrusion |
| **Command & Control** | |
| Cameleon V5 | Track blending of multiple sensors, slew-to-cue of camera to radar, mapping functionality, zone management, video archiving and distribution, and alarm notification and management |
| Simultaneously Tracking | >500 Targets |
| **Counter Drone Technology** | |
| Radio Frequency Sensor | Standard RF Sensor Kit: 2.4 GHz / 5.8 GHz / Wi-Fi;<br>Extended Frequency Kit: 433 / 868 / 915 MHz / 1.2 GHz / Wi-Fi |
| Detection Range | Up to 3 km horizontal; 457 m vertical (variable with noise floor & environment) |
| Defeat Range | Up to 1.5 km horizontal; 457 m vertical (variable with noise floor & environment) |
| Operator Console | Provides two 17" HD displays, mouse, keyboard, and camera remote controller. Plus, a mobile tablet for RF detection and mitigation on the move. |

| Environmental | |
|---|---|
| Power Options | Battery, Vehicle and Shore Power |
| RF Power Output | Up to 30 Watts (dependent on control protocol, frequency, and antennas) |
| **Deployment** | |
| Mast Deploy and Fully Operational | < 60 seconds |
| System and Mast Stow | < 30 seconds |
| US Export Classification | ITAR VIIC |




## AMERICAS

7055 Troy Hill Dr. Suite 300
Elkridge, MD 21075 USA

## EUROPE

2 Kings Hill Avenue - Kings Hill
West Malling, Kent ME19 4AQ
United Kingdom

Antennvägen 6,
PO Box 737
SE-187 66 Täby
Sweden

## MIDDLE EAST

Wadi Al Fey St.
Building 60, Office # 302
New Ministries Exit /
Khalifa Park Area
Abu Dhabi, U.A.E.

Saudi Arabia
Office 127, First Floor
Akaria Plaza Building, Olaya Street
Riyadh, 11481, Saudi Arabia

## ASIA

10 Kallang Avenue #09-10,
Aperia Tower 2
Singapore 339510



The information contained in this page pertains to products that may be subject to the International Traffic in Arms Regulations (ITAR) (22 C.F.R. Sections 120-130) or the Export Administration Regulations (EAR) (15 C.F.R. Sections 730-774) depending upon specifications for the final product; jurisdiction and classification will be provided upon request. ©2022 Teledyne FLIR LLC. All rights reserved.



Revised on 09/27/22
LVSS ADA C-UAS_Datasheet-LTR 22-0927